



QN18F11X02B, Nylon Female Quick Disconnect For 22 - 18 AWG (.11 x .02)

By Burndy
Catalog # [QN18F11X02B](#)



Nylon Female Quick Disconnect For 22 - 18 AWG (.11 x .02).

Features

- Sleeved barrel
- Insulated connector eliminate the need for post installation insulation
- Funnel entry barrrel opening assures quick and easy wire insertion
- Dimpled female socket detent ensures firm grip

General

Catalog Number	QN18F11X02B
Connector Type	Female Quick Disconnect
Insulation	Y
Insulation Type	Nylon
Material	Brass
Plated	Y
Plating Type	Tin
Trade Name	FINGRIP™
Type	Disconnect Connectors
UPC	781810635933
UPC 14 Digit GTIN	00781810635933

Dimensions

Dimension - Length Overall inch	0.77 in
Dimension - Strip Length inch	3/8 in
Dimension - Width inch	0.11 in
Dimension - Width mm	3 mm

Electrical Ratings

Voltage - Maximum	300 V
-------------------	-------

Conductor Related

Conductor Range	#22 AWG to #16 AWG
Conductor Size	22 - 18 AWG
Conductor Type	• CU C Solid-Size • CU C Str-Size

Certifications And Compliance

Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	Yes
Standards - Industry Standards	UL310
Met	
Standards - RoHS Compliance	UI
Status	
UL Listed	No

Logistics

Carton Quantity	1000
Minimum Pack Quantity	1000
Pallet Quantity	99999

Product Assets

[Catalogs - BURNDY Master Catalog - Section B - Small Terminals](#)
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Sales Drawings - 50094210](#)
[Specifications - QN18F11X02B](#)