



QN18F18X02B, Nylon Female Quick Disconnect For 22 - 18 AWG (.19 x .02)

By Burndy
Catalog # [QN18F18X02B](#)



Nylon Female Quick Disconnect For 22 - 18 AWG (.19 x .02)

Features

- Sleeved barrel
- Insulated connector eliminate the need for post installation insulation
- Funnel entry barrel opening assures quick and easy wire insertion
- Dimpled female socket detent ensures firm grip

Specifications

Certification - cULus	Yes
Certification - UL Recognized	No
Certification - ETL	No
Standards - Industry Standards Met	UL310
Standards - RoHS Compliance Status	UI
Certification - CSA Approved	No
UL Listed	No

Conductor

Conductor Size	22 - 18 AWG
Conductor Type	• CU C Solid-Size • CU C Str-Size
Conductor Range	#22 AWG to #16 AWG

Configuration

Connector Type	Female Quick Disconnect
----------------	-------------------------

Current

Voltage - Maximum	300 V
-------------------	-------

Dimensions

Dimension - Width inch	0.19 in
Package Length	0.000 in
Dimension - Width mm	5 mm
Package Width	0.000 in
Package Weight	0.000 lb.
Package Height	0.000 in
Dimension - Strip Length inch	3/8 in
Dimension - Length Overall	0.79 in
inch	

General

Insulation Type	Nylon
Trade Name	FINGRIP™
Plated	Y
Insulation	Y
Type	Disconnect Connectors
UPC 12 Digit	781810292679
UPC 14 Digit GTIN	00781810292679
Material	Brass
Plating Type	Tin
UPC	781810292679

Logistics

Minimum Pack Quantity	1000
Carton Quantity	1000
Pallet Quantity	99999

Product Assets

[Catalog \[English\]](#)