



QP10F250D, Vinyl Female Quick Disconnect For 12 - 10 AWG (.25 x .03)

By Burndy
Catalog # QP10F250D



Vinyl Female Quick Disconnect For 12 - 10 AWG (.25 x .03)

Features

- Sleeved barrel
- Insulated connector eliminate the need for post installation insulation
- Funnel entry barrel opening assures quick and easy wire insertion
- Dimpled female socket detent ensures firm grip

Specifications

Certification - cULus	N
Certification - UL Recognized	N
Certification - ETL	No
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
Industry Standard(s)	UL467
Certification - CSA Approved	No
UL Listed	No

Conductor

Conductor - Copper Solid Size Range	N/A
Conductor Size	12 - 10 AWG
Conductor - Copper Str Size	• 16 AWG • 14 AWG
Conductor - Copper Str Size Range	16 AWG - 14 AWG
Conductor Type	CU C Str-Size

Configuration

Connector Type	Female Quick Disconnect
----------------	-------------------------

Current

Voltage - Maximum	600 V
-------------------	-------

Dimensions

Dimension - Width inch	0.29 in
Package Length	0.000 in
Dimension - Width mm	7 mm
Package Width	0.000 in
Dimension - F Width Center to Center inch	0.11 in
Dimension - B Length fraction	1/4 in
Package Weight	0.000 lb.
Dimension - B Length inch	0.25 in
Package Height	0.000 in
Dimension - Length Overall inch	1.00 in
Dimension - Thread Size	-

General

Insulation Type	Vinyl
Trade Name	FINGRIP™
Plated	Y
Insulation	Y
Type	Disconnect Connectors
UPC 12 Digit	781810020623
UPC 14 Digit GTIN	00781810020623
Material	Brass
Plating Type	Tin
UPC	781810020623

Logistics

Minimum Pack Quantity	50
Carton Quantity	600
Pallet Quantity	99999

Product Assets

[Catalog \[English\]](#)