



QP10M250D, Vinyl Male Quick Disconnect For 12 - 10 AWG (.25 x .03)

By Burndy
Catalog # [QP10M250D](#)



Vinyl Male Quick Disconnect For 12 - 10 AWG (.25 x .03)

Features

- Butted seam
- Insulated connectors eliminate the need for post installation insulation
- Funnel entry barrel opening for quick and easy wire insertion
- Dimpled female socket detent ensure firm grip

Specifications

Certification - cULus	No
Certification - UL Recognized	No
Certification - ETL	No
Standards - Industry Standards Met	UL310
Standards - RoHS Compliance Status	CM
Industry Standard(s)	UL467
Certification - CSA Approved	Yes
UL Listed	Yes

Conductor

Conductor Size	12 - 10 AWG
Conductor - Copper Str Size	• 12 AWG • 10 AWG
Conductor - Copper Str Size Range	12 AWG-10 AWG
Conductor Type	CU C Str-Size

Configuration

Connector Type	Male Quick Disconnect
----------------	-----------------------

Current

Voltage - Maximum	600 V
-------------------	-------

Dimensions

Package Length	0.000 in
Package Width	0.000 in
Package Weight	0.000 lb.
Dimension - Pad Width inch	0.25 in
Package Height	0.000 in
Dimension - Length Overall inch	1.12 in
Dimension - D inch	0.35 in
Dimension - N inch	0.18 in

General

Insulation Type	Vinyl
Trade Name	FINGRIP™
Plated	Y
Insulation Type	Y
Type	Disconnect Connectors
UPC 12 Digit	781810020647
UPC 14 Digit GTIN	00781810020647
Material	Brass
Plating Type	Tin
UPC	781810020647

Logistics

Minimum Pack Quantity	50
Carton Quantity	600
Pallet Quantity	99999

Product Assets

[Catalog \[English\]](#)



A Hubbell brand