



**QP10M25X03D, Vinyl Male Quick Disc, 12-10 AWG (.25 x .03)**

By Burndy  
Catalog # [QP10M25X03D](#)

Vinyl Male Quick Disconnect For 12 - 10 AWG (.25 x .03), Butted Seam, Funnel Entry



**Features**

- Butted seam
- Funnel entry barrel opening for quick and easy wire insertion
- Mates with dimpled female socket detent for a firm grip

**Application**

Male Disconnect

**Specifications**

|                                    |       |
|------------------------------------|-------|
| Certification - UL Recognized      | No    |
| Buy American Compliant             | No    |
| Certification - cULus              | Yes   |
| Industry Standard(s)               | UL467 |
| Certification - ETL                | No    |
| Standards - Industry Standards Met | UL310 |
| Standards - RoHS Compliance        | CM    |
| Status                             |       |
| UL Listed                          | No    |
| Certification - CSA Approved       | No    |

**Conductor**

|                 |                    |
|-----------------|--------------------|
| Conductor Size  | 12 - 10 AWG        |
| Conductor Type  | CU C Str-Size      |
| Conductor Range | #12 AWG to #10 AWG |

**Configuration**

|                |                       |
|----------------|-----------------------|
| Connector Type | Male Quick Disconnect |
|----------------|-----------------------|

**Current**

|                   |       |
|-------------------|-------|
| Voltage - Maximum | 600 V |
|-------------------|-------|

**Dimensions**

|                                 |           |
|---------------------------------|-----------|
| Package Height                  | 0.000 in  |
| Package Weight                  | 0.000 lb. |
| Package Length                  | 0.000 in  |
| Package Width                   | 0.000 in  |
| Dimension - Strip Length inch   | 3/8 in    |
| Dimension - Width mm            | 6 mm      |
| Dimension - Width inch          | 0.25 in   |
| Dimension - Length Overall inch | 0.93 in   |

**General**

|                   |                       |
|-------------------|-----------------------|
| Product Family    | COMPRESSION           |
| Insulation Type   | Vinyl                 |
| Trade Name        | FINGRIP™              |
| Insulation        | Y                     |
| Plated            | Yes                   |
| Sub Brand         | HYDENT                |
| Product Type      | Terminal              |
| UPC               | 781810525067          |
| Type              | Disconnect Connectors |
| Material          | Brass                 |
| Plating Type      | Tin                   |
| UPC 12 Digit      | 781810525067          |
| UPC 14 Digit GTIN | 00781810525067        |

**Logistics**

|                       |       |
|-----------------------|-------|
| Minimum Pack Quantity | 50    |
| Pallet Quantity       | 99999 |
| Carton Quantity       | 600   |

**Product Assets**

[Catalog \[English\]](#)