



QP14F11X02D, Vinyl Female Quick Disc, 16-14 AWG (.11 x .02)

By Burndy
Catalog # [QP14F11X02D](#)

Vinyl Female Quick Disconnect For 16 - 14 AWG (.11 x .02), Butted Seam, Funnel Entry

Features

- Butted seam
- Insulated connectors eliminate the need for post installation insulation
- Funnel entry barrel opening for quick and easy wire insertion
- Dimpled female socket detent ensure firm grip

Application

Female Disconnect

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - Industry Standards Met	UL310
Standards - RoHS Compliance	CM
Status	
Buy American Compliant	No
Certification - cULus	Yes
Industry Standard(s)	UL467
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor Size	16 - 14 AWG
Conductor Type	CU C Str-Size
Conductor Range	#14 AWG to #16 AWG

Configuration

Connector Type	Female Quick Disconnect
----------------	-------------------------

Current

Voltage - Maximum	600 V
-------------------	-------



Dimensions

Package Height	0.000 in
Package Weight	0.000 lb.
Dimension - Width mm	3 mm
Dimension - Width inch	0.11 in
Package Length	0.000 in
Package Width	0.000 in
Dimension - Length Overall inch	0.75 in
Dimension - Strip Length inch	3/8 in

General

Plated	Yes
Product Family	COMPRESSION
Insulation Type	Vinyl
Trade Name	FINGRIP™
Sub Brand	HYDENT
Product Type	Terminal
UPC	781810480267
Type	Disconnect Connectors
Insulation	Y
Material	Brass
Plating Type	Tin
UPC 12 Digit	781810480267
UPC 14 Digit GTIN	00781810480267

Logistics

Minimum Pack Quantity	100
Carton Quantity	1200

Product Assets

[Catalog \[English\]](#)