



Vinyl Female Quick Disconnect For 16 - 14 AWG (.19 x .02)

By Burndy
Catalog # [QP14F18X02B](#)

Brass Female Quick Disconnect, 14-16 AWG, Vinyl Insulated, Tin Plated, Bulk Packaging.



General

Catalog Number	QP14F18X02B
Connector Type	Female Quick Disconnect
Insulation	Y
Insulation Type	Vinyl
Material	Brass
Plated	Y
Plating Type	Tin
Trade Name	FINGRIP™
Type	Disconnect Connectors
UPC	781810292730
UPC 12 Digit	7818102927300

Dimensions

Dimension - Length Overall inch	0.79 in
Dimension - Strip Length inch	3/8 in
Dimension - Width inch	0.187 in
Dimension - Width mm	5 mm

Electrical Ratings

Voltage - Maximum	600 V
-------------------	-------

Conductor Related

Conductor Range	#14 AWG to #16 AWG
Conductor Size	16 - 14 AWG
Conductor Type	• CU C Solid-Size • CU C Str-Size

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	Yes
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	1000
Pallet Quantity	99999

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Catalogs - Section B - Small Compression](#)
[Sales Drawings - 50094207](#)



A proud member of the Hubbell Family.