



QP14F18X02D, Vinyl Female Quick Disc, 16-14 AWG (.19 x .02)

By Burndy
Catalog # QP14F18X02D

Vinyl Female Quick Disconnect For 16 - 14 AWG (.19 x .02), Butted Seam, Funnel Entry

Features

- Butted seam
- Insulated connectors eliminate the need for post installation insulation
- Funnel entry barrel opening for quick and easy wire insertion
- Dimpled female socket detent ensure firm grip

Application

For quickly connecting or disconnecting a terminal

Specifications

Certification - UL Recognized	No
Certification - cULus	Yes
Industry Standard(s)	UL467
Certification - ETL	No
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance	CM
Status	
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor Size	16 - 14 AWG
Conductor Type	CU C Str-Size
Conductor Range	#14 AWG to #16 AWG

Configuration

Connector Type	Female Quick Disconnect
----------------	-------------------------

Current

Voltage - Maximum	600 V
-------------------	-------



Dimensions

Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - Strip Length inch	3/8 in
Dimension - Width mm	5 mm
Dimension - Width inch	0.187 in
Dimension - Length Overall inch	0.79 in

General

Product Family	COMPRESSION
Insulation Type	Vinyl
Trade Name	FINGRIP™
Insulation	Y
Plated	Yes
Sub Brand	FINGRIP
Product Type	Terminal
UPC	781810293379
Type	Disconnect Connectors
Material	Brass
Plating Type	Tin
UPC 12 Digit	781810293379
UPC 14 Digit GTIN	00781810293379

Logistics

Pallet Quantity	99999
Carton Quantity	1200

Product Assets

[Catalog \[English\]](#)