



QP14F25X03B, Vinyl Female Quick Disconnect For 16 - 14 AWG (.25 x .03)

By Burndy
Catalog # QP14F25X03B

Vinyl Female Quick Disconnect For 16 - 14 AWG (.25 x .03)

Features

- Butted seam
- Insulated connectors eliminate the need for post installation insulation
- Funnel entry barrel opening for quick and easy wire insertion
- Dimpled female socket detent ensure firm grip

Application

For quickly connecting or disconnecting a terminal

Specifications

Buy American Compliant	Contact Manufacturer
Certification - cULus	Yes
EU RoHS Indicator	Yes
Certification - UL Recognized	No
Certification - ETL	No
Standards - Industry Standards Met	UL310
Standards - RoHS Compliance Status	CM
Certification - CSA Approved	No
UL Listed	No
Buy America(n) Qualified	Contact Manufacturer

Conductor

Conductor Size	16 - 14 AWG
Conductor Type	• CU C Solid-Size • CU C Str-Size
Conductor Range	#14 AWG to #16 AWG

Configuration

Connector Type	Female Quick Disconnect
----------------	-------------------------

Current



Voltage - Maximum	600 V
-------------------	-------

Dimensions

Dimension - Width inch	0.25 in
Package Length	0.000 in
Dimension - Width mm	6 mm
Package Width	0.000 in
Package Weight	0.000 lb.
Package Height	0.000 in
Dimension - Strip Length inch	3/8 in
Dimension - Length Overall	0.87 in
inch	

General

Sub Brand	FINGRIP
Insulation Type	Vinyl
Trade Name	FINGRIP™
Plated	Y
Insulation	Y
Type	Disconnect Connectors
UPC 12 Digit	781810292754
UPC 14 Digit GTIN	00781810292754
Material	Brass
Plating Type	Tin
UPC	781810292754

Logistics

Minimum Pack Quantity	1000
Carton Quantity	1000
Pallet Quantity	99999

Product Assets

[Catalog \[English\]](#)