



QP14F25X03BG25, Vinyl Female Quick Disconnect For 16 - 14 AWG (.25 x .03)

By Burndy

Catalog # [QP14F25X03BG25](#)

Vinyl Female Quick Disconnect For 16 - 14 AWG (.25 x .03)



Features

- Butted seam
- Insulated connectors eliminate the need for post installation insulation
- Funnel entry barrel opening for quick and easy wire insertion
- Dimpled female socket detent ensure firm grip

Application

For quickly connecting or disconnecting a terminal

Specifications

Buy American Compliant	Contact Manufacturer
Certification - cULus	No
EU RoHS Indicator	Yes
Certification - UL Recognized	No
Certification - ETL	No
Standards - Industry Standards Met	UL310
Standards - RoHS Compliance Status	CM
Industry Standard(s)	UL467
Certification - CSA Approved	Yes
UL Listed	Yes
Buy America(n) Qualified	Contact Manufacturer

Conductor

Conductor Size	16 - 14 AWG
Conductor - Copper Str Size	• 16 AWG • 14 AWG
Conductor - Copper Str Size Range	16 AWG - 14 AWG
Conductor Type	CU C Str-Size

Configuration

Connector Type

Female Quick Disconnect

Dimensions

Dimension - Width inch	0.26 in
Package Length	0.000 in
Package Width	0.000 in
Dimension - F Width Center to Center inch	0.08 in
Dimension - B Length fraction	1/5 in
Package Weight	0.000 lb.
Dimension - B Length inch	0.20 in
Package Height	0.000 in
Dimension - Length Overall inch	0.85 in

General

Sub Brand	FINGRIP
Insulation Type	Vinyl
Trade Name	FINGRIP™
Plated	Y
Insulation	Y
Type	Disconnect Connectors
UPC 14 Digit GTIN	00781810486238
Material	Brass
Plating Type	Tin
UPC	781810486238

Logistics

Minimum Pack Quantity	5
Carton Quantity	5
Pallet Quantity	11625

Product Assets

[Catalog \[English\]](#)