



QP14M11X02D, Vinyl Male Quick Disconnect For 16 - 14 AWG (.11 x .02)

By Burndy
Catalog # [QP14M11X02D](#)

Vinyl Male Quick Disconnect For 16 - 14 AWG (.11 x .02)



Features

- Butted seam
- Funnel entry barrel opening for quick and easy wire insertion
- Mates with dimpled female socket detent for a firm grip

Application

Male Disconnect

Specifications

Buy American Compliant	No
Certification - cULus	Yes
EU RoHS Indicator	Yes
Certification - UL Recognized	No
Certification - ETL	No
Standards - Industry Standards Met	UL310
Standards - RoHS Compliance Status	CM
Certification - CSA Approved	No
UL Listed	No

Conductor

Conductor Size	16 - 14 AWG
Conductor Type	• CU C Solid-Size • CU C Str-Size
Conductor Range	#14 AWG to #16 AWG

Configuration

Connector Type	Male Quick Disconnect
----------------	-----------------------

Dimensions

Dimension - Width inch	0.11 in
Package Length	0.000 in
Dimension - Width mm	3 mm
Package Width	0.000 in
Package Weight	0.000 lb.
Package Height	0.000 in
Dimension - Strip Length inch	3/8 in
Dimension - Length Overall inch	0.76 in

General

Sub Brand	FINGRIP
Insulation Type	Vinyl
Trade Name	FINGRIP™
Plated	Y
Insulation	Y
Type	Disconnect Connectors
UPC 12 Digit	781810530672
UPC 14 Digit GTIN	00781810530672
Material	Brass
Plating Type	Tin
UPC	781810530672

Logistics

Minimum Pack Quantity	100
Carton Quantity	1200

Product Assets

[Catalog \[English\]](#)