



QP14M25X03D, Vinyl Male Quick Disc, 16-14 AWG (.25 x .03)

By Burndy
Catalog # [QP14M25X03D](#)

Vinyl Male Quick Disconnect For 16 - 14 AWG (.25 x .03), Butted Seam, Funnel Entry



Features

- Butted seam
- Funnel entry barrel opening for quick and easy wire insertion
- Mates with dimpled female socket detent for a firm grip

Application

For quickly connecting or disconnecting a terminal

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance	CM
Status	
Certification - cULus	Yes
Industry Standard(s)	UL467
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor Size	16 - 14 AWG
Conductor Type	CU C Str-Size
Conductor Range	#14 AWG to #16 AWG

Configuration

Connector Type	Male Quick Disconnect
----------------	-----------------------

Current

Voltage - Maximum	600 V
-------------------	-------

Dimensions

Package Height	0.000 in
Package Weight	0.000 lb.
Dimension - Width mm	6 mm
Dimension - Width inch	0.25 in
Package Length	0.000 in
Package Width	0.000 in
Dimension - Length Overall inch	0.84 in
Dimension - Strip Length inch	3/8 in

General

Plated	Yes
Product Family	COMPRESSION
Insulation Type	Vinyl
Trade Name	FINGRIP™
Sub Brand	FINGRIP
Product Type	Terminal
UPC	781810293485
Type	Disconnect Connectors
Insulation	Y
Material	Copper
Plating Type	Tin
UPC 12 Digit	781810293485
UPC 14 Digit GTIN	00781810293485

Logistics

Pallet Quantity	99999
Carton Quantity	1200

Product Assets

[Catalog \[English\]](#)