



QP18F11X02D, Vinyl Female Quick Disconnect For 22 - 18 AWG (.11 x .02)

By Burndy
Catalog # QP18F11X02D

Vinyl Female Quick Disconnect For 22 - 18 AWG (.11 x .02)

Features

- Butted seam
- Insulated connectors eliminate the need for post installation insulation
- Funnel entry barrel opening for quick and easy wire insertion
- Dimpled female socket detent ensure firm grip

Application

Female Disconnect

Specifications

Buy American Compliant	Contact Manufacturer
Certification - cULus	Yes
EU RoHS Indicator	Yes
Certification - UL Recognized	No
Certification - ETL	No
Standards - Industry Standards Met	UL310
Standards - RoHS Compliance Status	CM
Industry Standard(s)	UL467
Certification - CSA Approved	No
UL Listed	No
Buy America(n) Qualified	Contact Manufacturer

Conductor

Conductor Size	22 - 18 AWG
Conductor Type	CU C Str-Size
Conductor Range	#16 AWG to #22 AWG

Configuration

Connector Type	Female Quick Disconnect
----------------	-------------------------



Current

Voltage - Maximum	600 V
-------------------	-------

Dimensions

Dimension - Width inch	0.11 in
Package Length	0.000 in
Dimension - Width mm	3 mm
Package Width	0.000 in
Package Weight	0.000 lb.
Package Height	0.000 in
Dimension - Strip Length inch	3/8 in
Dimension - Length Overall inch	0.75 in

General

Sub Brand	HYDENT
Insulation Type	Vinyl
Trade Name	FINGRIP™
Plated	Y
Insulation	Y
Type	Disconnect Connectors
UPC 12 Digit	781810480250
UPC 14 Digit GTIN	00781810480250
Material	Brass
Plating Type	Tin
UPC	781810480250

Logistics

Minimum Pack Quantity	100
Carton Quantity	1200

Product Assets

[Catalog \[English\]](#)