



QP18F25X03B, Vinyl Female Quick Disconnect For 22 - 18 AWG (.25 x .03)

By Burndy
Catalog # QP18F25X03B

Vinyl Female Quick Disconnect For 22 - 18 AWG (.25 x .03)



Features

- Butted seam
- Insulated connectors eliminate the need for post installation insulation
- Funnel entry barrel opening for quick and easy wire insertion
- Dimpled female socket detent ensure firm grip

Specifications

Certification - cULus	Yes
Certification - UL Recognized	No
Certification - ETL	No
Standards - Industry Standards Met	UL310
Standards - RoHS Compliance Status	CM
Certification - CSA Approved	No
UL Listed	No

Conductor

Conductor Size	22 - 18 AWG
Conductor Type	• CU C Solid-Size • CU C Str-Size
Conductor Range	#16 AWG to #22 AWG

Configuration

Connector Type	Female Quick Disconnect
----------------	-------------------------

Current

Voltage - Maximum	600 V
-------------------	-------

Dimensions

Dimension - Width inch	0.25 in
Package Length	0.000 in
Dimension - Width mm	6 mm
Package Width	0.000 in
Package Weight	0.000 lb.
Package Height	0.000 in
Dimension - Strip Length inch	3/8 in
Dimension - Length Overall	0.87 in
inch	

General

Insulation Type	Vinyl
Trade Name	FINGRIP™
Plated	Y
Insulation	Y
Type	Disconnect Connectors
UPC 12 Digit	781810292662
UPC 14 Digit GTIN	00781810292662
Material	Brass
Plating Type	Tin
UPC	781810292662

Logistics

Minimum Pack Quantity	1000
Carton Quantity	1000
Pallet Quantity	99999

Product Assets

[Catalog \[English\]](#)