



QP18F25X03BG25, Vinyl Female Quick Disconnect For 22 - 18 AWG (.25 x .03)

By Burndy
Catalog # QP18F25X03BG25

Vinyl Female Quick Disconnect For 22 - 18 AWG (.25 x .03)

Features

- Butted seam
- Insulated connectors eliminate the need for post installation insulation
- Funnel entry barrel opening for quick and easy wire insertion
- Dimpled female socket detent ensure firm grip

Specifications

Certification - cULus	No
Certification - UL Recognized	No
Certification - ETL	No
Standards - Industry Standards Met	UL310
Standards - RoHS Compliance Status	CM
Industry Standard(s)	UL467
Certification - CSA Approved	Yes
UL Listed	Yes

Conductor

Conductor Size	22 - 18 AWG
Conductor - Copper Str Size	• 20 AWG • 18 AWG
Conductor - Copper Str Size Range	22 AWG - 18 AWG
Conductor Type	CU C Str-Size

Configuration

Connector Type	Female Quick Disconnect
----------------	-------------------------

Dimensions



Dimension - Width inch	0.26 in
Package Length	0.000 in
Package Width	0.000 in
Dimension - F Width Center to Center inch	0.08 in
Dimension - B Length fraction	1/5 in
Package Weight	0.000 lb.
Dimension - B Length inch	0.20 in
Package Height	0.000 in
Dimension - Length Overall inch	0.87 in

General

Insulation Type	Vinyl
Trade Name	FINGRIP™
Plated	Y
Insulation	Y
Type	Disconnect Connectors
UPC 14 Digit GTIN	00781810486252
Material	Brass
Plating Type	Tin
UPC	781810486252

Logistics

Minimum Pack Quantity	5
Carton Quantity	5
Pallet Quantity	11625

Product Assets

[Catalog \[English\]](#)