



QP18M25X03B, Vinyl Male Quick Disconnect For 22 - 18 AWG (.25 x .03)

By Burndy
Catalog # [QP18M25X03B](#)



Vinyl Male Quick Disconnect For 22 - 18 AWG (.25 x .03)

Features

- Butted seam
- Funnel entry barrel opening for quick and easy wire insertion
- Mates with dimpled female socket detent for a firm grip

Specifications

Certification - cULus	Yes
Certification - UL Recognized	No
Certification - ETL	No
Standards - Industry Standards Met	UL310
Standards - RoHS Compliance Status	CM
Certification - CSA Approved	No
UL Listed	No

Conductor

Conductor Size	22 - 18 AWG
Conductor Type	• CU C Solid-Size • CU C Str-Size
Conductor Range	#16 AWG to #22 AWG

Configuration

Connector Type	Male Quick Disconnect
----------------	-----------------------

Current

Voltage - Maximum	600 V
-------------------	-------

Dimensions

Dimension - Width inch	0.25 in
Dimension - Width mm	6 mm
Dimension - Strip Length inch	3/8 in
Dimension - Length Overall inch	0.84 in

General

Insulation Type	Vinyl
Trade Name	FINGRIP™
Plated	Y
Insulation	Y
Type	Disconnect Connectors
UPC 12 Digit	781810292716
UPC 14 Digit GTIN	00781810292716
Material	Brass
Plating Type	Tin
UPC	781810292716

Logistics

Minimum Pack Quantity	1000
Carton Quantity	1000
Pallet Quantity	99999

Product Assets

[Catalog \[English\]](#)