



QPX342CY, Mech. Parallel Clamp, Cu/Al, Mult. Configurations

By Burndy
Catalog # QPX342CY

Run 250-500 kcmil, Tap #6-#2 AWG, Capable of Tee, Cross, Parallel, Butt and Tap Configurations, Tin Plated



Features

- VERSITAP™ Type QPX-Y Parallel Clamps for copper or aluminum are capable of Tee, Cross, Parallel, Butt and Tap configurations
- Range-taking, only 10 connectors are required to accommodate conductor sizes from #6 Stranded to 1000 kcmil
- Edges are rounded for easy taping

Specifications

Certification - UL Recognized	No
Certification - cULus	No
Certification - ETL	No
Standards - RoHS Compliance	EX
Status	
Certification - UL Listed Direct Burial	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AL Str Run Range	250 kcmil-500 kcmil
Conductor - AL Str Run	• 250 kcmil • 266 kcmil • 300 kcmil • 336 kcmil • 350 kcmil • 397 kcmil • 400 kcmil • 450 kcmil • 477 kcmil • 500 kcmil
Conductor - AL Str Tap Range	6 AWG-2 AWG
Conductor - AL Str Tap	• 6 AWG • 4 AWG • 3 AWG • 2 AWG
Conductor - Copper Str Run Range	250 kcmil-500 kcmil
Conductor - Copper Str Run	• 250 kcmil • 300 kcmil • 350 kcmil • 400 kcmil • 450 kcmil • 500 kcmil

Conductor Type	• AL C Str-Run • CU C Str-Run • AL C Str-Tap • CU C Str-Tap
Conductor - Copper Str Tap Range	6 AWG-2 AWG
Conductor - Copper Str Tap	• 6 AWG • 5 AWG • 4 AWG • 3 AWG • 2 AWG

Configuration

Connector Type	Universal Clamp
----------------	-----------------

Dimensions

Package Height	0.000 in
Dimension - Height mm	55.6 mm
Dimension - Height inch	2.19
Dimension - Height fraction	2-1/4 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	38 mm
Dimension - Width fraction	2-1/8 in
Dimension - Width mm	54 mm
Dimension - Width inch	2.14
Dimension - Length Overall inch	1.50 in

Force Related

Installation Torque	375 LBS/in
Recommended in-lb	

General

Trade Name	VERSITAP™
Material - Hardware	DURIUM™ Silicon Bronze
Physical Attribute - Screw Type	Hexagonal Bolt
Plated	Y
UPC	781810342701
Material	Copper
Plating Type	Tin
UPC 12 Digit	781810342701
UPC 14 Digit GTIN	00781810342701

Logistics

Minimum Pack Quantity	3
Pallet Quantity	1908
Carton Quantity	9

Operational

Temperature Rating	194
--------------------	-----

Product Assets

[Catalog \[English\]](#)



A Hubbell brand