



QPX4434, Mech. Parallel Clamp for Cu, Mult. Configurations

By Burndy
Catalog # QPX4434



Run 500-1000 kcmil, Tap 250-500 kcmil, Capable of Tee, Cross, Parallel, Butt and Tap Configurations

Features

- VERSITAP™ Type QPX Parallel Clamps for copper are capable of Tee, Cross, Parallel, Butt and Tap configurations
- Range-taking, only 10 connectors are required to accommodate conductor sizes from #6 Stranded to 1000 kcmil
- Edges are rounded for easy taping

Application

For Tee, Cross, Parallel, Butt And Tap Connections

Specifications

Certification - UL Recognized	No
Buy American Compliant	Contact Manufacturer
Certification - cULus	No
Buy America(n) Qualified	Contact Manufacturer
Industry Standard(s)	UL 486A-486B
Certification - ETL	No
Standards - Industry Standards Met	UL486C
Standards - RoHS Compliance	EX
Status	
Certification - UL Listed Direct Burial	No
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - Nominal Diameter	0.114, 0.128, 0.144, 0.162, 0.600, 0.630, 0.681, 0.728, 0.772, 0.813, 0.893, 0.893, 0.964, 0.998, 1.031, 1.031, 1.094, 1.151
Conductor - Copper Str Run Range	500 kcmil-1000 kcmil
Conductor - Copper Str Run	• 500 kcmil • 550 kcmil • 600 kcmil • 700 kcmil • 750 kcmil • 800 kcmil • 850 kcmil • 900 kcmil • 1000 kcmil
Conductor Type	• CU C Str-Run • CU C Str-Tap
Conductor - Copper Str Tap Range	250 kcmil-500 kcmil
Conductor - Copper Str Tap	• 250 kcmil • 300 kcmil

- 350 kcmil
- 400 kcmil
- 450 kcmil
- 500 kcmil

Configuration

Connector Type	Universal Clamp
----------------	-----------------

Current

Rating - Minimum Voltage	600
--------------------------	-----

Dimensions

Package Height	0.000 in
Dimension - Height mm	77.7 mm
Dimension - Height inch	3.06
Dimension - Height fraction	3-1/16
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	52 mm
Dimension - Width fraction	2-7/16 in
Dimension - Width mm	62 mm
Dimension - Width inch	2.44
Dimension - Length Overall inch	2.06 in

Force Related

Installation Torque Recommended in-lb	240 LBS/in
---------------------------------------	------------

General

Product Family	MECHANICAL
Trade Name	VERSITAP™
Material - Hardware	DURIUM™ Silicon Bronze
Plated	No
Sub Brand	VERSITAP
Product Type	Run/Tap
UPC	781810345504
Type	QPX
Material	Copper
Plating Type	Unplated
UPC 12 Digit	781810345504
UPC 14 Digit GTIN	00781810345504

Logistics

Minimum Pack Quantity	1
-----------------------	---

Pallet Quantity	900	Temperature Rating	194
Carton Quantity	3		

Operational

Product Assets

[Catalog \[English\]](#)



A Hubbell brand