



QPX4444Y, Mech. Parallel Clamp, Cu/Al, Mult. Configurations

By Burndy

Catalog # [QPX4444Y](#)

750-1000 kcmil Cu Run/Tap, Capable of Tee, Cross, Parallel, Butt and Tap Configurations, Tin Plated



Features

- VERSITAP™ Type QPX-Y Parallel Clamps for copper or aluminum are capable of Tee, Cross, Parallel, Butt and Tap configurations
- Range-taking, only 10 connectors are required to accommodate conductor sizes from #6 Stranded to 1000 kcmil
- Edges are rounded for easy taping

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	EX
Status	
Certification - cULus	No
Certification - UL Listed Direct Burial	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Run Range	750 kcmil-1000 kcmil
Conductor - Copper Str Run	• 750 kcmil • 800 kcmil • 850 kcmil • 900 kcmil • 1000 kcmil
Conductor - AL Str Run Range	750 kcmil-1000 kcmil
Conductor - AL Str Run	• 750 kcmil • 795 kcmil • 800 kcmil • 874 kcmil • 900 kcmil • 954 kcmil • 1000 kcmil
Conductor - AL Str Tap Range	750 kcmil-1000 kcmil
Conductor - AL Str Tap	• 750 kcmil • 795 kcmil • 800 kcmil • 874 kcmil • 900 kcmil • 954 kcmil • 1000 kcmil
Conductor Type	• AL C Str-Run

- CU C Str-Run
 - AL C Str-Tap
 - CU C Str-Tap
- 750 kcmil-1000 kcmil
- 750 kcmil
 - 800 kcmil
 - 850 kcmil
 - 900 kcmil
 - 1000 kcmil

Conductor - Copper Str Tap Range

Conductor - Copper Str Tap

Configuration

Connector Type	Universal Clamp
----------------	-----------------

Dimensions

Dimension - Height mm	96 mm
Dimension - Height inch	3.78
Dimension - Height fraction	3-7/8 in
Dimension - Width mm	89 mm
Dimension - Width inch	3.5
Dimension - L Length Overall mm	89 mm
Dimension - Width fraction	3-1/2 in
Dimension - Length Overall inch	3.50 in

Force Related

Installation Torque Recommended in-lb	500 LBS/in
---------------------------------------	------------

General

Plated	Y
Trade Name	VERSITAP™
Material - Hardware	DURIUM™ Silicon Bronze
UPC	781810006146
Material	Copper
Plating Type	Tin
UPC 12 Digit	781810006146
UPC 14 Digit GTIN	00781810006146

Logistics

Minimum Pack Quantity	4
-----------------------	---

Operational

Temperature Rating	194
--------------------	-----



A Hubbell brand