



Ratchet Cable Cutter, Cuts up to 1000 kcmil Copper and Aluminum, Maximum Insulation Diameter 2.375"

By Burndy
Catalog # [RCC1000](#)

Ratchet Cable Cutter, 1000 kcmil CU/AL

Features

- Patented high strength steel blades
- Quick release, bi-directional ratchet mechanism
- Rapid blade advance

Application

Cutting

Specifications

Buy American Compliant	Contact Manufacturer
EU RoHS Indicator	Yes
Standards - RoHS Compliance Status	EX
Buy America(n) Qualified	Contact Manufacturer

Dimensions

Length	20 in
Cable Insulation Diameter Maximum	2.375 in



Width	2 in
Weight	4.5 lb.
Height	6 in
Dimensions	20 in x 2 in x 6 in

General

Sub Brand	RATCHET CUTTER
Application - For Use On	Aluminum, Copper Cable
Type	Cutter
UPC 12 Digit	781810174883
UPC 14 Digit GTIN	00781810174883
Tool Type	Ratchet Cable Cutter
UPC	781810174883

Logistics

Package Contents	Tool only
Minimum Pack Quantity	1

Product Assets

[Catalog \[English\]](#)