



**Ratchet Cable Cutter, Cuts up to 336 kcmil ACSR, up to 500 kcmil Aluminum, up to 350 kcmil Copper**

By Burndy  
Catalog # [RCC336](#)



Ratchet Cable Cutter, Cuts up to 336 kcmil ACSR, up to 500 kcmil Aluminum, up to 350 kcmil Copper.

**General**

|                          |                              |
|--------------------------|------------------------------|
| Application - For Use On | ACSR, Aluminum, Copper Cable |
| Catalog Number           | RCC336                       |
| EU RoHS Indicator        | Yes                          |
| Tool Type                | Ratchet Cable Cutter         |
| Type                     |                              |
| UPC                      | 781810459980                 |
| UPC 12 Digit             | 7818104599800                |

**Dimensions**

|                                   |                              |
|-----------------------------------|------------------------------|
| Cable Insulation Diameter Maximum | 1.25 in                      |
| Dimensions                        | 10.50 in x 3.50 in x 1.25 in |
| Height                            | 1.25 in                      |
| Length                            | 10.5 in                      |
| Weight                            | 1.2 lb                       |
| Width                             | 3.5 in                       |

**Certifications And Compliance**

Standards - RoHS Compliance EX  
Status

**Logistics**

Package Contents Tool only

**Product Assets**

[Catalogs - Full Line BURNDY Catalog](#)  
[Product Cross Section Image\(s\) - BUR\\_RCC336\\_LA](#)  
[Sales Drawings - 10082457](#)



A proud member of the Hubbell Family.