



Ratchet Cable Cutter, Cuts up to 600 kcmil
Soft Drawn Copper and Aluminum,
Maximum Insulation Diameter 1.05"

By Burndy
Catalog # [RCC600E](#)

Ratchet Cable Cutter, 600 kcmil CU/AL

Features

- Patented high strength steel blades
- Quick release, bi-directional ratchet mechanism
- Rapid blade advance

Application

Cutting

Specifications

Standards - RoHS Compliance EX
Status

Conductor

- Crimping Ranges
- Cutting Capacity: Copper 600 kcmil
 - Aluminum: 600 kcmil

Dimensions

Package Height 0.000 in
Length 10.5 in
Package Weight 0.000 lb.
Package Length 0.000 in



Package Width	0.000 in
Weight	1.2 lb.
Height	4.5 in
Width	1.25 in
Cable Insulation Diameter	1.050 in
Maximum Dimensions	10.5 in x 1.25 in x 4.5 in

General

Application - For Use On	Aluminum, Copper Cable
Tool Type	Ratchet Cable Cutter
UPC	781810488195
Type	Cutter
UPC 12 Digit	781810488195
UPC 14 Digit GTIN	00781810488195

Logistics

Package Contents	Tool only
------------------	-----------

Product Assets

[Catalog \[English\]](#)
[Installation Manual \[French, English\]](#)