



Ratchet Cable Cutter, Cuts up to 750 kcmil Copper and Aluminum, Maximum Insulation Diameter 1.62"

By Burndy
Catalog # [RCC750HD](#)

Ratchet Cable Cutter, 750 kcmil CU/AL

Features

- Patented high strength steel blades
- Quick release, bi-directional ratchet mechanism
- Rapid blade advance

Application

Cutting

Specifications

Buy American Compliant	No
EU RoHS Indicator	Yes
Standards - RoHS Compliance Status	EX

Dimensions

Package Length	0.000 in
Package Width	0.000 in
Package Weight	0.000 lb.
Package Height	0.000 in
Length	10.35 in



Cable Insulation Diameter Maximum	1.620 in
Width	1.75 in
Weight	2.56 lb.
Height	4.69 in
Dimensions	10.35 in x 1.75 in x 4.69 in

General

Sub Brand	RATCHET CUTTER
Application - For Use On	Aluminum, Copper Cable
Type	Cutter
UPC 12 Digit	781810350058
UPC 14 Digit GTIN	00781810350058
Tool Type	Ratchet Cable Cutter
UPC	781810350058

Logistics

Package Contents	Tool only
Minimum Pack Quantity	1

Product Assets

[Catalog \[English\]](#)