



Ratchet Cable Cutter, Cuts up to 954 kcmil ACSR, up to 1000 kcmil Copper and Aluminum, Maximum Insulation Dia. 1.38"

By Burndy
Catalog # [RCC954ACSR1K](#)

Ratchet Cable Cutter, ACSR, CU/AL, 1.38"

Features

- Patented high strength steel blades
- Quick release, bi-directional ratchet mechanism
- Rapid blade advance

Application

Cutting

Specifications

Buy American Compliant	No
EU RoHS Indicator	Yes
Standards - RoHS Compliance	EX
Status	

Dimensions

Length	22.75 in
Cable Insulation Diameter Maximum	1.380 in
Width	1.88 in



Weight	6.5 lb.
Height	7 in
Dimensions	22.75 in x 1.88 in x 7 in

General

Sub Brand	RATCHET CUTTER
Application - For Use On	ACSR, Aluminum, Copper Cable
Type	Cutter
UPC 12 Digit	781810480595
UPC 14 Digit GTIN	00781810480595
Tool Type	Ratchet Cable Cutter
UPC	781810480595

Logistics

Package Contents	Tool only
Minimum Pack Quantity	1

Product Assets

[Catalog \[English\]](#)