


RDM628, Aluminum - Multiple Outlet Connector (RDM Mole)

By Burndy
Catalog # [RDM628](#)

URD Mole, #4 Str. - 250 kcmil Al or Cu 300 kcmil - 350 kcmil, 600 Volt Rating, 8.78 in L



Features

- Type RDM-28 MOLE connectors are an economical, insulated, submersible service junction suitable for direct burial or for use in enclosures
- Disconnectable Joints allow additions of new services without disturbing previous installations
- Taping is eliminated, Heat Shrink or Force-Fit Rubber Sleeves insulated each joint, Rubber is used to insulate the MOLE body
- Removable sealing covers are supplied on all outlets but two
- REA Listed Tap Kits, including HYLUG, Hardware and Sleeve are ordered separately

Application

For Aluminum And Copper And Direct Burial Or For Use In Enclosures

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	CM
Buy American Compliant	No
Certification - cULus	No
EU RoHS Indicator	Yes
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AL Str Size	• 4 AWG • 3 AWG • 2 AWG • 1 AWG • 1/0 AWG • 2/0 AWG • 3/0 AWG • 4/0 AWG • 250 kcmil • 266 kcmil • 300 kcmil • 336 kcmil • 350 kcmil
-------------------------	---

Conductor - AL Str Size Range 4 AWG-350 kcmil

Conductor - Copper Str Size Range	4 AWG-250 kcmil
Conductor - Copper Str Size	• 4 AWG • 3 AWG • 2 AWG • 1 AWG • 1/0 • 2/0 AWG • 3/0 AWG • 4/0 AWG • 250 kcmil

Configuration

Number Of Outlets	6
Connector Type	Tap

Dimensions

Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - Length Overall	8.78 in
inch	

General

Insulation Type	Rubber
Trade Name	MOLE™
Sub Brand	URD MOLE
UPC	781810180051
Type	RDM-28
Insulation	Y
Material	Aluminum Alloy
UPC 12 Digit	781810180051
UPC 14 Digit GTIN	00781810180051

Logistics

Minimum Pack Quantity	6
Pallet Quantity	1
Carton Quantity	12

Product Assets

[Catalog \[English\]](#)