



Remote Hydraulic Cutter, 10000 psi, Cuts up to 1.29" Copper and Aluminum, 1113 kcmil ACSR

By Burndy
Catalog # [RHCC129ACSR](#)

Remote Latch Head 1.29" CU/AL, 1113 ACSR

Features

- Interference free closure for mid-span cuts
- Precision cutting blades for clean cuts
- High strength steel cylinder
- Light weight, ergonomic design
- Durable canvas carrying bag stores tool and accessories

Application

Cutting

Specifications

EU RoHS Indicator	Yes
Standards - RoHS Compliance	EX
Status	
Buy America(n) Qualified	Contact Manufacturer

Dimensions

Length	11.41 in
Width	3.65 in
Weight	6.21 lb.
Height	2.33 in
Dimensions	11.41 in x 3.65 in x 2.33 in



General

Application - For Use On	• ACSR, Aluminum, Copper Cable • Ground Rod • Rebar • Soft Steel Bolts • Standard Guy • EHS Guy Strand
Type	Cutter
UPC 12 Digit	781810372357
UPC 14 Digit GTIN	00781810372357
Tool Type	Remote Hydraulic Cutter
UPC	781810372357

Logistics

Package Contents	Tool, Canvas Carry Bag
Minimum Pack Quantity	1
Carton Quantity	1
Pallet Quantity	168

Product Assets

[Catalog \[English\]](#)