



Remote Hydraulic Cutter, 10000 psi, Cuts up to 2156 kcmil ACSR, up to 2.00" Copper and Aluminum

By Burndy
Catalog # [RHCC2156ACSR](#)

Remote Latch Head 2.00" CU/AL, 2156 ACSR

Features

- 180° head rotation
- Durable hardened, precision steel blades
- Specialized latch head for mid-span cuts
- Durable canvas carrying bag stores tool and accessories

Application

Cutting

Specifications

Standards - RoHS Compliance UI
Status

Dimensions

Length	13.17 in
Width	2.69 in
Weight	10 lb.



Height	4.13 in
Dimension - Thread Size	-
Dimensions	13.17 in x 2.69 in x 4.13 in

General

Application - For Use On	ACSR, Aluminum, Copper Cable
Type	Cutter
UPC 12 Digit	781810671559
UPC 14 Digit GTIN	00781810671559
UPC	781810671559

Logistics

Package Contents	Tool, Nylon Carry Bag
Minimum Pack Quantity	1

Product Assets

[Catalog \[English\]](#)