



Remote Hydraulic Cutter, 10000 psi, Cuts up to 2.45" O.D. Copper and Aluminum

By Burndy
Catalog # [RHCC245CUAL](#)

Remote Latch Head 2.45" O.D. CU/AL



Features

- Interference free closure for mid-span cuts
- Precision cutting blades for clean cuts
- High strength steel cylinder
- Light weight, ergonomic design
- Durable canvas carrying bag stores tool and accessories

Application

Cutting

Specifications

Standards - RoHS Compliance EX
Status

Dimensions

Length 14.8 in
Width 4.74 in

Weight 8.4 lb.
Height 2.45 in
Dimensions 14.8 in x 4.74 in x 2.45 in

General

Application - For Use On Aluminum, Copper Cable
Type Cutter
UPC 12 Digit 781810439791
UPC 14 Digit GTIN 00781810439791
Tool Type Remote Hydraulic Cutter
UPC 781810439791

Logistics

Package Contents Tool, Nylon Carry Bag
Minimum Pack Quantity 1

Product Assets

[Catalog \[English\]](#)