



Remote Hydraulic Cutter, 10000 psi, Cuts up to 4.00" O.D. Copper and Aluminum

By Burndy
Catalog # [RHCC4CUAL](#)

Remote Scissor Head, 4.00" O.D. CU/AL



Features

- Specialized scissor head design for interference free closure for mid-span cuts
- High strength hardened steel cutting blades
- 360° swivel hose fitting
- Stainless Steel lifting assist eyebolt
- Light weight ergonomic design

Application

Cutting

Specifications

Standards - RoHS Compliance UI
Status

Dimensions

Width	5.15 in
Weight	19.9 lb.
Height	9.13 in
Length	21.29 in
Dimensions	21.29 in x 5.15 in x 9.13 in

General

Type	Cutter
UPC	781810665855
Application - For Use On	Aluminum, Copper Cable

Logistics

Package Contents	Tool, Canvas Carry Bag
Minimum Pack Quantity	1

Product Assets

[Catalog \[English\]](#)