



RYA28UCR, Tap Kit - HYLUG Terminal, Rubber Sleeve, Hardware (RDM Mole)

By Burndy
Catalog # [RYA28UCR](#)

Force Fit Rubber Sleeve Tap Kit, 4/0 Str(Al/Cu), 4/0 Str-250 Comp(Al), 249 or 840 Index



Features

- Kit consists of Universal HYLUG, Mounting Hardware and Pre-Lubricated Forcefit Rubber Sleeve
- HYLUG is a pre-filled with PENETROX joint compound and sealed

Application

FOR ALUMINUM OR COPPER FOR USE WITH TYPE RDM-28 URD MOLE

Specifications

Certification - UL Recognized	No
Buy American Compliant	No
Certification - cULus	No
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AL Str Size	• 4/0 AWG • 250 kcmil
Conductor - AL Str Size Range	4/0 AWG-250 kcmil
Conductor - Copper Str Size	4/0 AWG
Conductor - Copper Str Size Range	4/0 AWG

Configuration

Physical Attribute - Number of Crimps Required	1
Physical Attribute - Number of Holes	1
Connector Type	Terminal

Dimensions

Dimension - Pad Width inch	0.91 in
Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - Strip Length inch	1-11/16
Dimension - B Length inch	1.62 in
Dimension - D inch	0.91 in
Dimension - Length Overall inch	2.74 in

General

Insulation Type	Rubber
Trade Name	MOLE™
Die Index	• 249 • K-840
Insulation Plated	Y No
Sub Brand	TAP KITS, MOLE
Product Type	Compression
UPC	781810181959
Type	RYA-UCR
Plating Type	Unplated
UPC 14 Digit GTIN	00781810181959

Logistics

Minimum Pack Quantity	1
Pallet Quantity	2160
Carton Quantity	9

Product Assets

[Catalog \[English\]](#)