



RYA2UCHEX3SS, URD Mole Tap Assembl,  
Stainless Steel Hardware

By Burndy  
Catalog # [RYA2UCHEX3SS](#)

URDMOLE TAP ASSY W/SS H



Specifications

|                                    |    |
|------------------------------------|----|
| Certification - ETL                | No |
| Certification - UL Recognized      | No |
| Standards - RoHS Compliance Status | CM |
| Certification - cULus              | No |
| UL Listed                          | No |
| Certification - CSA Approved       | No |

Conductor

|                                     |                                                                                           |
|-------------------------------------|-------------------------------------------------------------------------------------------|
| Conductor - Copper Solid Size       | 1/0 AWG                                                                                   |
| Conductor - Copper Solid Size Range | 1/0 AWG                                                                                   |
| Conductor - AL Str Size             | <ul style="list-style-type: none"><li>• 2 AWG</li><li>• 1 AWG</li><li>• 1/0 AWG</li></ul> |
| Conductor - AL Str Size Range       | 2 AWG-1/0 AWG                                                                             |
| Conductor - Copper Str Size Range   | 2 AWG-1 AWG                                                                               |
| Conductor - Copper Str Size         | <ul style="list-style-type: none"><li>• 2 AWG</li><li>• 1 AWG</li></ul>                   |

Configuration

|                                                |             |
|------------------------------------------------|-------------|
| Physical Attribute - Number of Crimps Required | 1           |
| Connector Type                                 | Heat Shrink |

Dimensions

|                                 |           |
|---------------------------------|-----------|
| Dimension - Pad Width inch      | 0.65 in   |
| Package Height                  | 0.000 in  |
| Package Weight                  | 0.000 lb. |
| Package Length                  | 0.000 in  |
| Package Width                   | 0.000 in  |
| Dimension - B Length inch       | 0.96 in   |
| Dimension - D inch              | 0.65 in   |
| Dimension - Length Overall inch | 2 in      |

General

|                   |                                                                    |
|-------------------|--------------------------------------------------------------------|
| Trade Name        | MOLE™                                                              |
| Die Index         | <ul style="list-style-type: none"><li>• 243</li><li>• BG</li></ul> |
| UPC               | 781810042564                                                       |
| UPC 12 Digit      | 781810042564                                                       |
| UPC 14 Digit GTIN | 00781810042564                                                     |

Logistics

|                       |      |
|-----------------------|------|
| Minimum Pack Quantity | 3    |
| Pallet Quantity       | 2664 |
| Carton Quantity       | 9    |

Product Assets

[Catalog \[English\]](#)