

Substation - Aluminum Rigid Spacer

By Burndy
Catalog # [S2GBP41A12](#)



Substation Connectors

Features

- Streamlined rigid spacer for large range of cables
- 1 bolt per clamping module
- EHV Rated: Self-Shielding up to 550kV

Application

Substation

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AAAC 5005 Size Range	927.2 (37) kcmil
Conductor - AAAC 6201 Size Range	927.2 (37) kcmil
Conductor - AAAC 6201 Size	927.2 (37) kcmil
Conductor - AL Str Size	• 795 kcmil • 800 kcmil • 874 kcmil
Conductor - AAAC 5005 Size	927.2 (37) kcmil
Conductor - AL Str Size Range	795 kcmil-874 kcmil
Conductor - ACSR Str Size	715.5 (26/7) Starling kcmil
Conductor - ACSR Str Size Range	715.5 (26/7) Starling kcmil

Configuration

Connector Type	Spacer
----------------	--------

Dimensions

Dimension - Height mm	0 mm
Dimension - Width mm	76 mm
Dimension - Width inch	3.00 in
Dimension - L Length Overall mm	305 mm
Dimension - B Length inch	3.00 in
Dimension - Diameter Min Size inch	1.026 in
Dimension - Diameter Max Size inch	1.092 in
Dimension - Length Overall inch	12.00 in

General

Plated	N
UPC	781810234198
Material	Aluminum Alloy
Plating Type	Unplated
UPC 12 Digit	781810234198
UPC 14 Digit GTIN	00781810234198

Logistics

Pallet Quantity	1
Carton Quantity	1

Product Assets

[Catalog \[English\]](#)