



Substation - Aluminum Rigid Spacer

By Burndy
Catalog # [S2GBP445A8](#)



Two Conductor 8 IN Spacer, 954 kcmil-1033.5 kcmil ACSR, 1033.5 kcmil-1113 kcmil AAC

Features

- Streamlined rigid spacer for large range of cables
- 1 bolt per clamping module
- EHV Rated: Self-Shielding up to 550kV

Application

Substation

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	EX
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AL Str Size	• 1033 kcmil • 1100 kcmil • 1113 kcmil
Conductor - AL Str Size Range	1033 kcmil-1113 kcmil
Conductor - ACSR Str Size	• 954 (45/7) Rail kcmil • 954 (54/7) Cardinal kcmil • 1033.5 (45/7) Ortolan kcmil
Conductor - ACSR Str Size Range	954 (45/7) Rail kcmil-1033.5 (45/7) Ortolan kcmil

Configuration

Connector Type	Spacer
----------------	--------

Dimensions

Package Height	0.000 in
Dimension - Height mm	0 mm
Length	8 in
Package Weight	0.000 lb.
Dimension - Width mm	76 mm
Dimension - Width inch	3.00 in
Package Length	0.000 in
Package Width	0.000 in
Dimension - B Length inch	3.00 in
Width	3 in

Force Related

Installation Torque	480 lbs-in
Recommended in-lb	

General

Plated	N
UPC	781810337783
Material	Aluminum Alloy, Cast
Plating Type	Unplated
UPC 12 Digit	781810337783
UPC 14 Digit GTIN	00781810337783

Logistics

Minimum Pack Quantity	1
Pallet Quantity	144
Carton Quantity	4

Product Assets

[Catalog \[English\]](#)