

Substation - Aluminum Rigid Spacer

By Burndy
Catalog # [S2GBP44A12](#)



Substation Connectors

Features

- Streamlined rigid spacer for large range of cables
- 1 bolt per clamping module
- EHV Rated: Self-Shielding up to 550kV

Application

Substation

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	EX
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AL Str Size	954 kcmil
Conductor - AL Str Size Range	954 kcmil
Conductor - ACSR Str Size	• 795 (54/7) Condor kcmil • 795 (26/7) Drake kcmil • 795 (30/19) Mallard kcmil • 874.5 (54/7) Crane kcmil
Conductor - ACSR Str Size Range	795 (54/7) Condor kcmil-874.5 (54/7) Crane kcmil

Configuration

Connector Type	Spacer
----------------	--------

Dimensions

Package Height	0.000 in
Dimension - Height mm	0 mm
Package Weight	0.000 lb.
Dimension - Width mm	76 mm
Dimension - Width inch	3.00 in
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	305 mm
Dimension - B Length inch	3.00 in
Dimension - Diameter Min Size inch	1.092 in
Dimension - Diameter Max Size inch	1.165 in
Dimension - Length Overall inch	12.00 in

General

Plated	N
UPC	781810234228
Material	Aluminum Alloy
Plating Type	Unplated
UPC 12 Digit	781810234228
UPC 14 Digit GTIN	00781810234228

Logistics

Minimum Pack Quantity	2
Pallet Quantity	1
Carton Quantity	1

Product Assets

[Catalog \[English\]](#)