

Substation - Aluminum Rigid Spacer

By Burndy
Catalog # [S2GBP46A12](#)



Two Conductor 12 IN Cable Spacer, 1590 kcmil-1600 kcmil AAC,
1272 kcmil-1431 kcmil ACSR, 550kV

Features

- Streamlined rigid spacer for large range of cables
- 1 bolt per clamping module
- EHV Rated: Self-Shielding up to 550kV

Application

Substation

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	EX
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AL Str Size	• 1590 kcmil • 1600 kcmil
Conductor - AL Str Size Range	1590 kcmil-1600 kcmil
Conductor - ACSR Str Size	• 1272 (54/19) Pheasant kcmil • 1431 (54/19) Plover kcmil
Conductor - ACSR Str Size Range	1272 (54/19) Pheasant kcmil-1431 (54/19) Plover kcmil

Configuration

Connector Type	Spacer
----------------	--------

Dimensions

Dimension - Pad Width inch	3.00 in
Dimension - Height mm	73 mm
Dimension - Height inch	2.87 in
Dimension - Width mm	76 mm
Dimension - Width inch	3.00 in
Dimension - L Length Overall mm	363 mm
Dimension - B Length inch	3.00 in
Dimension - Diameter Min Size inch	1.382 in
Dimension - Diameter Max Size inch	1.504 in
Dimension - Length Overall inch	14.30 in

General

UPC	781810254394
Material	Aluminum Alloy
Plating Type	Unplated
UPC 12 Digit	781810254394
UPC 14 Digit GTIN	00781810254394

Logistics

Minimum Pack Quantity	24
Pallet Quantity	1
Carton Quantity	1

Product Assets

[Catalog \[English\]](#)