



Substation - Aluminum Rigid Spacer

By Burndy
Catalog # [S2GBP486A](#)



Two Conductor 18 IN Spacer, 2156 kcmil-2167 kcmil ACSR, 2300 kcmil-2500 kcmil AAC

Features

- Streamlined rigid spacer for large range of cables
- 1 bolt per clamping module
- EHV Rated: Self-Shielding up to 550kV

Application

Substation

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AL Str Size	• 2300 kcmil • 2500 kcmil
Conductor - AL Str Size Range	2300 kcmil-2500 kcmil
Conductor - ACSR Str Size	• 2156 (84/19) Bluebird kcmil • 2167 (72/7) Kiwi kcmil
Conductor - ACSR Str Size Range	2156 (84/19) Bluebird kcmil-2167 (72/7) Kiwi kcmil

Configuration

Connector Type	Spacer
----------------	--------

Dimensions

Package Height	0.000 in
Dimension - Height mm	72.6 mm
Package Weight	0.000 lb.
Dimension - Width mm	76 mm
Dimension - Width inch	3.00 in
Package Length	0.000 in
Package Width	0.000 in
Dimension - B Length inch	3.00 in
Dimension - Diameter Min Size	1.737 in
inch	
Dimension - Diameter Max Size	1.824 in
inch	

Force Related

Installation Torque	480 lbs-in
Recommended in-lb	

General

Plated	N
UPC	781810146996
Material	Aluminum Alloy, Cast
Plating Type	Unplated
UPC 12 Digit	781810146996
UPC 14 Digit GTIN	00781810146996

Logistics

Pallet Quantity	1
Carton Quantity	1

Product Assets

[Catalog \[English\]](#)