



Substation - Aluminum Rigid Spacer

By Burndy
Catalog # [S2GBP48A](#)



Two Conductor 18 IN Spacer, 1590(45/7) kcmil-1750(84/19) kcmil
ACSR, 1750 kcmil-2000 kcmil AAC, 550kV

Features

- Streamlined rigid spacer for large range of cables
- 1 bolt per clamping module
- EHV Rated: Self-Shielding up to 550kV

Application

Substation

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	EX
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AL Str Size	• 1750 kcmil • 1800 kcmil • 1900 kcmil • 2000 kcmil
Conductor - AL Str Size Range	1750 kcmil-2000 kcmil
Conductor - ACSR Str Size	• 1590 (45/7) kcmil • 1590 (54/19) kcmil • 1750 (54/19) kcmil • 1750 (84/19) kcmil
Conductor - ACSR Str Size Range	1590 (45/7) kcmil-1750 (84/19) kcmil

Configuration

Connector Type	Spacer
----------------	--------

Dimensions

Package Height	0.000 in
Dimension - Height mm	83.3 mm
Package Weight	0.000 lb.
Dimension - Width mm	76 mm
Dimension - Width inch	3.00 in
Package Length	0.000 in
Package Width	0.000 in
Dimension - B Length inch	3.00 in
Dimension - Diameter Min Size	1.504 in
Dimension - Diameter Max Size	1.632 in

Force Related

Installation Torque	480 lbs-in
Recommended in-lb	

General

Plated	N
UPC	781810273418
Material	Aluminum Alloy, Cast
Plating Type	Unplated
UPC 12 Digit	781810273418
UPC 14 Digit GTIN	00781810273418

Logistics

Pallet Quantity	1
Carton Quantity	1

Product Assets

[Catalog \[English\]](#)