

Substation - Aluminum Rigid Spacer

By Burndy
Catalog # [S2GBP48A12B4](#)

Substation Connectors



Features

- Streamlined rigid spacer for large range of cables
- 1 bolt per clamping module
- EHV Rated: Self-Shielding up to 550kV

Application

Substation

Specifications

Standards - RoHS Compliance	EX
Status	
Certification - CSA Approved	No

Conductor

Conductor - AL Str Size	• 1750 kcmil • 1800 kcmil • 1900 kcmil • 2000 kcmil
Conductor - AL Str Size Range	1750 kcmil-2000 kcmil
Conductor - ACSR Str Size	• 1590 (45/7) Lapwing kcmil • 1590 (54/19) Falcon kcmil • 1780 (54/19) kcmil
Conductor - ACSR Str Size Range	1590 (45/7) Lapwing kcmil-1780 (54/19) kcmil

Configuration

Connector Type	Spacer
----------------	--------

Dimensions

Package Height	0.000 in
Dimension - Height mm	73.4 mm
Dimension - Height inch	2.89 in
Package Weight	0.000 lb.
Dimension - Width mm	102 mm
Dimension - Width inch	4.00 in
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	432 mm
Dimension - B Length inch	4.00 in
Dimension - Length Overall inch	17.00 in

General

Plated	N
UPC	781810279014
Material	Aluminum Alloy
Plating Type	Unplated
UPC 12 Digit	781810279014
UPC 14 Digit GTIN	00781810279014

Logistics

Minimum Pack Quantity	1
Pallet Quantity	1
Carton Quantity	1

Product Assets

[Catalog \[English\]](#)