



By Burndy
Catalog # [S2GBP48A8](#)



Two Conductor 8 IN Spacer, 1590 kcmil-1750 kcmil ACSR, 1750 kcmil-2000 kcmil AAC

Features

- Streamlined rigid spacer for large range of cables
- 1 bolt per clamping module
- EHV Rated: Self-Shielding up to 550kV

Application

Substation

Specifications

Standards - RoHS Compliance Status	EX
UL Listed	No

Conductor

Conductor - ACSR Str Size	1590 (45/7) kcmil;1590 (54/19) kcmil;1750 (54/19) kcmil;1750 (84/19) kcmil
Conductor - ACSR Str Size Range	1590 (45/7) kcmil-1750 (84/19) kcmil
Conductor - AL Str Size	1750 kcmil;1800 kcmil;1900 kcmil;2000 kcmil
Conductor - AL Str Size Range	1750 kcmil-2000 kcmil

Dimensions

Dimension - Width inch	3.00 in
Dimension - Width mm	76 mm
Dimension - Height mm	83.3 mm
Dimension - Diameter Max Size inch	1.632 in
Dimension - Diameter Min Size inch	1.504 in

Force Related

Installation Torque Recommended in-lb	480 lbs-in
---------------------------------------	------------

General

UPC 12 Digit	781810209714
UPC 14 Digit GTIN	00781810209714
Material	Aluminum Alloy, Cast
UPC	781810209714

Logistics

Carton Quantity	4
Minimum Pack Quantity	1

Product Assets

[Catalog \[English\]](#)