



Substation - Aluminum Rigid Spacer

By Burndy
Catalog # [S2GBP495A13B2GS](#)



Two Conductor 13 IN Spacer, 3500 kcmil AAC, 550kV

Application

Substation

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	CM
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AL Str Size Range	3500 kcmil
-------------------------------	------------

Configuration

Connector Type	Spacer
----------------	--------

Dimensions

Dimension - Height mm	90.4 mm
Dimension - Height inch	3.57 in
Dimension - Width mm	105 mm
Dimension - Width inch	4.12 in

Dimension - L Length Overall mm	400 mm
Dimension - B Length inch	4.12 in
Dimension - Length Overall inch	15.74 in

Force Related

Installation Torque	660 lbs-in
Recommended in-lb	

General

Plated	N
UPC	621945270756
Material	Aluminum Alloy, Cast
Plating Type	Unplated
UPC 12 Digit	621945270756
UPC 14 Digit GTIN	00621945270756

Logistics

Pallet Quantity	1
Carton Quantity	1

Product Assets

[Catalog \[English\]](#)