

Substation - Aluminum Rigid Spacer

By Burndy
Catalog # [S2GBPA486A8](#)



Two Conductor 8 IN Spacer, 2156 kcmil-2167 kcmil ACSR, 2300 kcmil-2500 kcmil AAC

Features

- Streamlined rigid spacer for large range of cables
- 1 bolt per clamping module
- EHV Rated: Self-Shielding up to 550kV

Application

Substation

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	EX
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AL Str Size	• 2300 kcmil • 2500 kcmil
Conductor - AL Str Size Range	2300 kcmil-2500 kcmil
Conductor - ACSR Str Size	• 2156 (84/19) Bluebird kcmil • 2167 (72/7) Kiwi kcmil
Conductor - ACSR Str Size Range	2156 (84/19) Bluebird kcmil-2167 (72/7) Kiwi kcmil

Configuration

Connector Type	Spacer
----------------	--------

Dimensions

Dimension - Height mm	72.6 mm
Dimension - Height inch	3.06 in
Dimension - Width mm	102 mm
Dimension - Width inch	4.00 in
Dimension - L Length Overall mm	268 mm
Dimension - B Length inch	4.00 in
Dimension - Length Overall inch	10.56 in

Force Related

Installation Torque	480 lbs-in
Recommended in-lb	

General

Plated	N
UPC	781810306062
Material	Aluminum Alloy, Cast
Plating Type	Unplated
UPC 12 Digit	781810306062
UPC 14 Digit GTIN	00781810306062

Logistics

Pallet Quantity	1
Carton Quantity	1

Product Assets

[Catalog \[English\]](#)