



Substation - Aluminum Rigid Spacer

By Burndy
Catalog # [S2R41ACG5](#)



Rigid Spacer, Accommodates: 795 KCMIL ASC

Application

Substation

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	CM
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Number Of Conductors	2
Conductor - Connection Combination	Cable Spacer
Conductor - AL Str Size	795 KCMIL
Conductor - AL Str Size Range	795 KCMIL
Conductor Spacing	6 in

Configuration

Connector Type	Spacer
----------------	--------

Dimensions

Package Height	0.000 in
Dimension - Height mm	50.8 mm
Dimension - Height inch	2.00 in
Package Weight	0.000 lb.

Dimension - Width mm	51 mm
Dimension - Width inch	2.00 in
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	191 mm
Dimension - Length Overall inch	7.50 in

Force Related

Installation Torque Recommended in-lb	480 LBS/in
---------------------------------------	------------

General

Plated	N
One Wrench Installation	Y
Clamping Element Design	2 Piece Design
UPC	621945167001
Material	Aluminum Alloy
UPC 12 Digit	621945167001
UPC 14 Digit GTIN	00621945167001

Logistics

Pallet Quantity	1
Carton Quantity	1

Product Assets

[Catalog \[English\]](#)