

Substation - Aluminum Rigid Spacer

By Burndy
Catalog # [S2R46ACG1](#)



Rigid 6 IN Spacer, 1590 kcmil , 230kV

Application

Substation

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	CM
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Connection Combination	Cable Spacer
Conductor - AL Str Size Range	1590 kcmil

Configuration

Connector Type	Spacer
----------------	--------

Dimensions

Package Height	0.000 in
Dimension - Height mm	0 mm
Dimension - Height inch	2.80 in
Package Weight	0.000 lb.
Dimension - Width mm	51 mm

Dimension - Width inch	2.00 in
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	149 mm
Dimension - B Length inch	2.00 in
Dimension - Length Overall inch	5.88 in

Force Related

Installation Torque Recommended in-lb	480 in-lb
---------------------------------------	-----------

General

Plated	N
UPC	781810529874
Material	Aluminum Alloy, Cast
Plating Type	Unplated
UPC 12 Digit	781810529874
UPC 14 Digit GTIN	00781810529874

Logistics

Pallet Quantity	1
Carton Quantity	1

Product Assets

[Catalog \[English\]](#)