



Substation - Aluminum Rigid Spacer

By Burndy
Catalog # [S2R493A6BCH](#)



Rigid 6 IN Spacer, 3000 kcmil ASC, 138kV

Application

Substation

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	CM
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Number Of Conductors	2
Conductor - Connection Combination	Cable Spacer
Conductor - AL Str Size Range	3000 kcmil

Configuration

Connector Type	Spacer
----------------	--------

Dimensions

Package Height	0.000 in
Dimension - Height mm	91.9 mm
Dimension - Height inch	3.62 in
Package Weight	0.000 lb.
Dimension - Width mm	76 mm
Dimension - Width inch	3.00 in

Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	238 mm
Dimension - B Length inch	3.00 in
Dimension - Length Overall inch	9.38 in

Force Related

Installation Torque Recommended in-lb	660 LBS/in
---------------------------------------	------------

General

Plated	N
One Wrench Installation	Y
Clamping Element Design	2 Piece Design
UPC	781810489291
Material	Aluminum Alloy, Cast
Plating Type	Unplated
UPC 12 Digit	781810489291
UPC 14 Digit GTIN	00781810489291

Logistics

Pallet Quantity	1
Carton Quantity	1

Product Assets

[Catalog \[English\]](#)