



Substation - Aluminum Rigid Spacer

By Burndy
Catalog # [S3GBP445A](#)

Three Conductor Spacer, 1033.5 kcmil-1113 kcmil AAC, 954(45/7) kcmil-1033.5(45/7) kcmil ACSR, 550kV



Features

- Streamlined rigid spacer for 3 cables in a triangular shape
- 1 bolt per clamping module
- EHV Rated: Self-Shielding up to 550kV

Application

Substation

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	EX
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AL Str Size	1033 kcmil 1100 kcmil 1113 kcmil
Conductor - AL Str Size Range	1033 kcmil-1113 kcmil
Conductor Type	- AL C Str-Size - ACSR C Str-Size
Conductor - ACSR Str Size	954 (45/7) Rail kcmil 954 (54/7) Cardinal kcmil 1033.5 (45/7) Ortolan kcmil
Conductor - ACSR Str Size Range	954 (45/7) Rail kcmil-1033.5 (45/7) Ortolan kcmil

Configuration

Connector Type	Spacer
----------------	--------

Dimensions

Package Height	0.000 in
Dimension - Height mm	0 mm
Package Weight	0.000 lb.
Dimension - Width mm	76 mm
Dimension - Width inch	3.00 in
Package Length	0.000 in
Package Width	0.000 in
Dimension - B Length inch	3.00 in
Dimension - Diameter Min Size inch	1.165 in
Dimension - Diameter Max Size inch	1.216 in

Force Related

Installation Torque Recommended in-lb	480 in-lb
---------------------------------------	-----------

General

Plated	N
UPC	781810246092
Material	Aluminum Alloy, Cast
Plating Type	Unplated
UPC 12 Digit	781810246092
UPC 14 Digit GTIN	00781810246092

Logistics

Minimum Pack Quantity	3
Pallet Quantity	1
Carton Quantity	1

Product Assets

[Catalog \[English\]](#)