

Substation - Aluminum Rigid Spacer

By Burndy
Catalog # [S3GBP46A](#)

Three Conductor Spacer, 1590 kcmil-1600 kcmil AAC, 1272(54/19) kcmil-1431(54/19) kcmil ACSR, 550kV



Features

- Streamlined rigid spacer for 3 cables in a triangular shape
- 1 bolt per clamping module
- EHV Rated: Self-Shielding up to 550kV

Application

Substation

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	EX
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AL Str Size	• 1590 kcmil • 1600 kcmil
Conductor - AL Str Size Range	1590 kcmil-1600 kcmil
Conductor Type	• AL C Str-Size • ACSR C Str-Size
Conductor - ACSR Str Size	• 1272 (54/19) Pheasant kcmil • 1351.5 (54/19) Martin kcmil • 1431 (54/19) Plover kcmil
Conductor - ACSR Str Size Range	1272 (54/19) Pheasant kcmil-1431 (54/19) Plover kcmil

Configuration

Connector Type	Spacer
----------------	--------

Dimensions

Package Height	0.000 in
Dimension - Height mm	0 mm
Package Weight	0.000 lb.
Dimension - Width mm	76 mm
Dimension - Width inch	3.00 in
Package Length	0.000 in
Package Width	0.000 in
Dimension - B Length inch	3.00 in
Dimension - Diameter Min Size	1.382 in
inch	
Dimension - Diameter Max Size	1.465 in
inch	

Force Related

Installation Torque	480 in-lb
Recommended in-lb	

General

Plated	N
UPC	781810251935
Material	Aluminum Alloy, Cast
Plating Type	Unplated
UPC 12 Digit	781810251935
UPC 14 Digit GTIN	00781810251935

Logistics

Minimum Pack Quantity	1
Pallet Quantity	1
Carton Quantity	1

Product Assets

[Catalog \[English\]](#)