

Substation - Aluminum Rigid Spacer

By Burndy
Catalog # [S3GBP486A](#)

Three Conductor Spacer, 2300 kcmil-2500 kcmil AAC,
2167(72/7) kcmil-2156(84/19) kcmil ACSR, 550kV



Features

- Streamlined rigid spacer for 3 cables in a triangular shape
- 1 bolt per clamping module
- EHV Rated: Self-Shielding up to 550kV

Application

Substation

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	EX
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AL Str Size	2300 kcmil 2500 kcmil
Conductor - AL Str Size Range	2300 kcmil-2500 kcmil
Conductor Type	- AL C Str-Size - ACSR C Str-Size
Conductor - ACSR Str Size	2156 (64/119) kcmil 2156 (84/19) Bluebird kcmil 2167 (72/7) Kiwi kcmil
Conductor - ACSR Str Size Range	2156 (64/119) kcmil-2167 (72/7) Kiwi kcmil

Configuration

Connector Type	Spacer
----------------	--------

Dimensions

Dimension - Height mm	0 mm
Dimension - Width mm	76 mm
Dimension - Width inch	3.00 in
Dimension - B Length inch	3.00 in
Dimension - Diameter Min Size inch	1.737 in
Dimension - Diameter Max Size inch	1.823 in

Force Related

Installation Torque	480 in-lb
Recommended in-lb	

General

Plated	N
UPC	781810259993
Material	Aluminum Alloy, Cast
Plating Type	Unplated
UPC 12 Digit	781810259993
UPC 14 Digit GTIN	00781810259993

Logistics

Pallet Quantity	1
Carton Quantity	1

Product Assets

[Catalog \[English\]](#)