

Substation - Aluminum Rigid Spacer

By Burndy
Catalog # [S3GBP48A](#)



Three Conductor Spacer, 1750 kcmil-2000 kcmil AAC, 1590(45/7) kcmil-1750(84/19) kcmil ACSR, 550kV

Application

Substation

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	EX
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Package Height	0.000 in
Dimension - Height mm	0 mm
Package Weight	0.000 lb.
Dimension - Width mm	76 mm
Dimension - Width inch	3.00 in
Package Length	0.000 in
Package Width	0.000 in
Dimension - B Length inch	3.00 in
Dimension - Diameter Min Size	1.502 in
inch	
Dimension - Diameter Max Size	1.630 in
inch	

Conductor

Conductor - AL Str Size	1750 kcmil 1800 kcmil 1900 kcmil 2000 kcmil
Conductor - AL Str Size Range	1750 kcmil-2000 kcmil
Conductor Type	- AL C Str-Size - ACSR C Str-Size
Conductor - ACSR Str Size	1590 (45/7) Lapwing kcmil 1590 (54/19) Falcon kcmil 1780 (54/19) kcmil
Conductor - ACSR Str Size Range	1590 (45/7) Lapwing kcmil-1780 (54/19) kcmil

Force Related

Installation Torque	480 in-lb
Recommended in-lb	

General

Plated	N
UPC	781810269626
Material	Aluminum Alloy, Cast
Plating Type	Unplated
UPC 12 Digit	781810269626
UPC 14 Digit GTIN	00781810269626

Logistics

Pallet Quantity	1
Carton Quantity	1

Configuration

Connector Type	Spacer
----------------	--------

Dimensions

Product Assets

[Catalog \[English\]](#)