



Substation - Aluminum Rigid Spacer

By Burndy
Catalog # [S3GBP48A13GS](#)

Three Conductor 13 IN Spacer, 1750 kcmil-2000 kcmil AAC,
1590(45/7) kcmil-1750(84/19) kcmil ACSR



Application

Substation

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	CM
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AL Str Size	1750 kcmil 1800 kcmil 1900 kcmil 2000 kcmil
Conductor - AL Str Size Range	1750 kcmil-2000 kcmil
Conductor Type	- AL C Str-Size - ACSR C Str-Size
Conductor - ACSR Str Size Range	1590 (45/7) kcmil-1750 (84/19) kcmil

Configuration

Connector Type	Spacer
----------------	--------

Dimensions

Package Height	0.000 in
Dimension - Height mm	353 mm
Dimension - Height inch	13.89 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	399 mm
Dimension - B Length inch	3.00 in
Dimension - Length Overall inch	15.69 in

General

UPC	781810529362
Material	Aluminum Alloy
Plating Type	Unplated
UPC 12 Digit	781810529362
UPC 14 Digit GTIN	00781810529362

Logistics

Pallet Quantity	1
Carton Quantity	1

Product Assets

[Catalog \[English\]](#)