

Substation - Aluminum Rigid Spacer

By Burndy
Catalog # [S3GBPA445A](#)

Substation Connectors



Features

- Streamlined rigid spacer for 3 cables in a triangular shape
- 1 bolt per clamping module
- EHV Rated: Self-Shielding up to 550kV

Application

Substation

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	EX
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AL Str Size	• 1033 kcmil • 1100 kcmil • 1113 kcmil
Conductor - AL Str Size Range	1033 kcmil-1113 kcmil
Conductor Type	• AL C Str-Size • ACSR C Str-Size
Conductor - ACSR Str Size	• 954 (45/7) Rail kcmil • 954 (54/7) Cardinal kcmil • 1033.5 (45/7) Ortolan kcmil • 1033.5 (54/7) Curlew kcmil
Conductor - ACSR Str Size Range	954 (45/7) Rail kcmil-1033.5 (54/7) Curlew kcmil

Configuration

Connector Type	Spacer
----------------	--------

Dimensions

Dimension - Pad Width inch	4.00 in
Dimension - Height mm	0 mm
Dimension - Width mm	76 mm
Dimension - Width inch	3.00 in
Dimension - F Width Center to Center inch	1.75 in
Dimension - B Length inch	3.00 in
Dimension - D inch	4.00 in

General

Plated	N
UPC	781810272244
Material	Aluminum Alloy
Plating Type	Unplated
UPC 12 Digit	781810272244
UPC 14 Digit GTIN	00781810272244

Logistics

Minimum Pack Quantity	1
Pallet Quantity	1
Carton Quantity	1

Product Assets

[Catalog \[English\]](#)